



COVERS & ACCESSORIES

Our Relax range of wheelchair cushion covers are all designed to offer protection to the user and the product.

The covers are either breathable or fluid repellent, stretchable and hand washable. A cover is included with each cushion, but they are also available to purchase separately.



Wipeable Black Outer Cover

Available with:

Easy (Also available for Duogel on request)

Materials:

Topside and Underside: Polyurethane transfer coating on a weft knitted polyester fabric.

Features:

Water resistant wipe down cover
Easy to clean & maintain

Standard Black Outer Cover

Available with:

Duogel, Gelcell, Gelcell G2, CoolCell, Trio

Materials:

Topside: Weft knitted polyester fabric with a polyurethane transfer coating on inner side.
Underside: Anti-slip nylon coated with flame retardant PU, which has been treated with a biocide.

Features:

Water resistant and easy to wash
High Grip /Anti-slip surface

Codes & Sizes:

Duogel Wipedown

DWC003-1414
DWC003-1514
DWC003-1517
DWC003-1616
DWC003-1618
DWC003-1717
DWC003-1719
DWC003-1816
DWC003-1818
DWC003-1820
DWC003-2018
DWC003-2020
DWC003-2218
DWC003-2418

Easy Wipedown

EC004-1416
EC004-1418
EC004-1616
EC004-1717
EC004-1816
EC004-1818
EC004-1820
EC004-2020
EC004-2218

Easy High Profile Wipedown

ECH005-1616
ECH005-1717
ECH005-1816
ECH005-1818
ECH005-1820
ECH005-2020

Codes & Sizes:

Duogel

DC003-1414
DC003-1514
DC003-1517
DC003-1616
DC003-1618
DC003-1717
DC003-1719
DC003-1816
DC003-1818
DC003-1820
DC003-2018
DC003-2020
DC003-2218
DC003-2418

Gelcell G2

GC005-1414
GC005-1515
GC005-1616
GC005-1618
GC005-1717
GC005-1816
GC005-1818

Gelcell, CoolCell

GC004-1514
GC004-1616
GC004-1717
GC004-1816
GC004-1818
GC004-2018

Trio

TC001-1416
TC001-1616
TC001-1717
TC001-1816
TC001-1818



Spacer Fabric Cover

Available with:

Gelcell, CoolCell

Materials:

Topside: Spacer fabric material enhances redistribution of pressure peaks and dispersion of air and water.

Underside: Anti-slip nylon polyurethane griplock.

Features:

- Excellent dispersion of air and moisture
- Enhances redistribution of pressure peaks
- Millions of microfilaments act as miniature pressure springs
- Highly durable
- Washable at 60°C
- High grip/anti-slip surface

Codes & Sizes:

Gelcell, CoolCell

- CC002-1514
- CC002-1616
- CC002-1717
- CC002-1816
- CC002-1818
- CC002-2018



Handi Pump

Aerogel dual action Handi Pump

Available with:

Gelcell, Gelcell G2, CoolCell

Code: AP001

Repair Kit

Available with:

Gelcell, Gelcell G2, CoolCell

Code: RPK005

The repair kit should be used as a temporary solution only.

